


CircuitSolver® Union Thermal Disinfection Dual Valve (CSUTD-D)
 [Thermostatic balancing valve with union body and two actuators]
SUBMITTAL

JOB:	ORDER NO:	DATE:
	SUBMITTED BY:	DATE:
UNIT TAG:	APPROVED BY:	DATE:
CITY:	ENGINEER:	BUILDING TYPE:
STATE:	CONTRACTOR:	CONSTRUCTION TYPE:
COMPLETION DATE:		

DESCRIPTION

CircuitSolver® is a thermostatic balancing valve that automatically and continuously adjusts flow to maintain the desired temperature in a domestic hot water supply line. Since the CircuitSolver® responds to water temperature to control the flow entering the recirculation line it eliminates the need to manually balance the system. The "CSUTD-D" version CircuitSolver® incorporates a second actuator to reopen the valve during a thermal disinfection process and an optional check valve.



Model No.	NPT	Diameter (D)		Length (L)		Weight		Standard Balancing C _v			Thermal Disinfection Balancing C _v		Max. Pressure		Max. Temp.	
		IN	MM	IN	MM	LBS.	KG	OPEN	CLOSED	DESIGN	OPEN	CLOSED	PSIG	BAR	°F	°C
CSUTD-D-½-XXX/170	1/2"	2.0	51	6.3	160	2.5	1.1	1.8	0.2	0.85	0.5	0.2	200	14	250	121
CSUTD-D-½-XXX/170-CV1																
CSUTD-D-¾-XXX/170	3/4"	2.0	51	6.3	160	2.5	1.1	1.8	0.2	0.85	0.5	0.2				
CSUTD-D-¾-XXX/170-CV1																
CSUTD-D-1-XXX/170	1"	2.4	60	6.7	169	4.0	1.8	3.3	0.2	1.57	0.5	0.2				
CSUTD-D-1-XXX/170-CV1																

Model Number Selection


XXX refers to the desired closing temperature for standard balancing. When the water temperature drops below this point the CircuitSolver® will begin to open, allowing water to easily enter the return line. The valve will start to reopen approximately 20°F above the standard balancing temperature and rebalance the system at 170°F. For example, if you want 120°F desired return temperature and the CSUTD-D is to be installed on a 3/4" line, the model number would be CSUTD-D-3/4-120-170. To add optional check valve insert -CV1 to the end of the model number. Ex. CSUTD-D-3/4-120-170-CV1

FLOW RATE CALCULATION USING "Cv" FACTOR SHOWN IN TABLE ABOVE


$$GPM = C_v \sqrt{\Delta P}$$

$$C_v = \sqrt{\frac{GPM}{\Delta P}}$$

$$\Delta P = \left[\frac{GPM}{C_v} \right]^2$$

MATERIALS		
		
ITEM	DESCRIPTION	MATERIAL
1	Valve Body w/ Union Threads	300 series stainless steel
2	Insert - CircuitSolver [®]	300 series stainless steel
3	Spring	300 series stainless steel
4	Plug	300 series stainless steel
5	Thermal Actuator	300 series stainless steel
6	Carrier	300 series stainless steel
7	Union Nut	300 series stainless steel
8	O-ring	BUNA
9	Check Valve (optional)	GLASS FILLED NORLYL
10	Insert - Female Threaded	300 series stainless steel

OPTIONAL CHECK VALVE	
Features and Benefits	
-100% factory tested drip tight operation	
-Snap fit design, no retainer needed	
-Extra-low head loss and low cracking pressure	
-External O-ring in groove	
Certifications	
-ANSI/ NSF 61	
ITEM	MATERIAL
Cap	Glass filled Noryl
Guide	Glass filled Noryl
Plunger	Glass filled Noryl
Lip Spring	EPDM rubber
Spring	Stainless Steel AISI 301
O-ring	EPDM rubber

OPTIONAL CHECK VALVE TECHNICAL DATA	
Medium: Clear water only	
Approximate Cracking Pressure: 0.29 PSI	
<div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> <p>Continuous</p>  <p>max. 120 °C max. 250 °F</p> </div> <div style="text-align: center;">  <p>150 psi max. 10 bar max.</p> </div> <div style="text-align: center;"> <p>Short-term (5 minutes max.)</p>  <p>max. 125 °C max. 260 °F</p> </div> <div style="text-align: center;">  <p>230 psi max. 16 bar max.</p> </div> </div>	

TYPICAL SPECIFICATION

- I. Furnish and install CIRCUITSOLVER[®] Union Thermal Disinfection Dual Balancing Valve as indicated on the plans. CIRCUITSOLVER[®] shall be self-contained and fully automatic without additional piping or control mechanisms. Valve shall be a CIRCUITSOLVER[®] as manufactured by ThermOmegaTech[®], Inc. or equivalent.
 - A. CIRCUITSOLVER[®] shall regulate the flow of recirculated domestic hot water based on water temperature entering the CIRCUITSOLVER[®] regardless of system operating pressure. As the water temperature increases the valve proportionally closes dynamically adjusting flow to meet the specified temperature.
 1. CIRCUITSOLVER[®] never fully closes, even at the desired set point. There is always sufficient bypass flow back to the recirculating pump to prevent overheating or “dead heading” of the pump.
 2. CIRCUITSOLVER[®] is set at the factory for the desired return temperature. No field adjustments needed. Several temperature set points are available.
 3. CIRCUITSOLVER[®] Union Thermal Disinfection Dual Balancing Valve shall be available in 1/2”, 3/4” & 1” NPT.
 - B. CIRCUITSOLVER[®] Union Thermal Disinfection Dual Balancing Valve allows for an additional balancing cycle at 170°F.
 1. The valve will start to re-open above the low temperature balancing set point to allow high temperature water through during a thermal disinfection process. The valve will rebalance at the second temperature set point.
- II. CIRCUITSOLVER[®] body and all internal components are made with lead-free materials with major components constructed of type 300 series SS.
 - A. CIRCUITSOLVER[®] shall be rated to 200 PSIG maximum working pressure.
 1. CIRCUITSOLVER[®] shall be standard tapered female pipe thread, NPT.
 - B. CIRCUITSOLVER[®] shall be rated to 250°F (121.1°C) maximum working temperature.
 - C. CIRCUITSOLVER[®] valve shall be NSF/ANSI/CAN 61 or 372 certified.
 - D. Thermal actuator shall be spring-loaded and self-cleaning, delivering closing thrust sufficient to keep orifice opening free of scale deposits.
- III. Installation of CIRCUITSOLVER[®] shall be made by qualified tradesmen. Install CIRCUITSOLVER[®] in each domestic hot water return piping branch beyond last hot water device in that branch.
 - A. Provide suitable line size isolation valves, unions, and strainer as indicated in piping detail shown on the drawings.
 - B. Provide suitable access panel as required in non-accessible ceilings and walls.
 - C. Pay close attention to flow arrow, especially with valves that have an integrated check valve.