

**CircuitSolver® Union Assembly Thermal Disinfection Dual Valve with Viega ProPress® Systems (CSUASTD-D-PP)**  
 [Thermostatic balancing valve with union body, ball valves, strainer, ProPress ends and two actuators]

**SUBMITTAL**

<b>JOB:</b>	<b>ORDER NO:</b>	<b>DATE:</b>
	<b>SUBMITTED BY:</b>	<b>DATE:</b>
<b>UNIT TAG:</b>	<b>APPROVED BY:</b>	<b>DATE:</b>
<b>CITY:</b>	<b>ENGINEER:</b>	<b>BUILDING TYPE:</b>
<b>STATE:</b>	<b>CONTRACTOR:</b>	<b>CONSTRUCTION TYPE:</b>
<b>COMPLETION DATE:</b>		

**DESCRIPTION**

CircuitSolver® is a thermostatic balancing valve that automatically and continuously adjusts flow to maintain the desired temperature in a domestic hot water supply line. Since the CircuitSolver® responds to water temperature to control the flow entering the recirculation line it eliminates the need to manually balance the system. The "CSUASTD-D-PP" version CircuitSolver® incorporates a second actuator to reopen the valve during a thermal disinfection process, an optional check valve, isolated ball valves, a strainer, and Viega® ProPress adapter fittings. The featured strainer (20 mesh) must be maintained in order to avoid flow obstruction.



**DIMENSIONS**

Item No.	Part Number	Description	Qty.	Item No.	Part Number	Description	Qty.	Item No.	Part Number	Description	Qty.
1	261-20X00X-XXX	CSUTD-D-1/2-XXX/YYY-(CV1)	1	1	261-30X00X-XXX	CSUTD-D-3/4-XXX/YYY-(CV1)	1	1	261-40X00X-XXX	CSUTD-D-1-XXX/YYY-(CV1)	1
2	92-162	1/2" x CL NIPPLE BRASS, LF	1	2	92-026	3/4" X CL NIPPLE BRASS, LF	1	2	92-044	1" X CL NIPPLE BRASS, LF	1
3	92-160	BALL VALVE, 1/2" MxF, LF	2	3	92-158	BALL VALVE, 3/4" MxF, LF	2	3	92-170	BALL VALVE, 1" MxF, LF	2
4	92-200	Y- STRAINER, 1/2" BRASS	1	4	92-201	Y- STRAINER, 3/4" BRASS	1	4	92-202	Y- STRAINER, 3/4" BRASS	1
5	92-090	ADAPTER, 1/2" NPT x 1/2" ProPress	2	5	92-091	ADAPTER, 3/4" NPT x 3/4" ProPress	2	5	92-092	ADAPTER, 1" NPT x 1" ProPress	2

\* ALL COMPONENTS ARE LEAD FREE

\* ALL COMPONENTS ARE LEAD FREE


\* ALL COMPONENTS ARE LEAD FREE




Model No.	NPT	Diameter (D)		Length (L)		Height (H1)		Height (H2)		Weight		Standard Balancing C <sub>v</sub>			Thermal Disinfection Balancing C <sub>v</sub>		Max. Pressure		Max. Temp	
		IN	MM	IN	MM	IN	MM	IN	MM	LBS.	KG	OPEN	CLOSED	DESIGN	OPEN	CLOSED	PSIG	BAR	°F	°C
CSUASTD-D-1/2-XXX/170-PP	1/2"	2.0	51	15.4	391	1.8	46	2.5	64	4.6	2.1	1.8	0.2	0.85	0.5	0.2	200	14	250	121
CSUASTD-D-1/2-XXX/170-CV1-PP																				
CSUASTD-D-3/4-XXX/170-PP	3/4"	2.0	51	17.3	439	2.0	51	3.3	84	6.0	2.7	1.8	0.2	0.85	0.5	0.2				
CSUASTD-D-3/4-XXX/170-CV1-PP																				
CSUASTD-D-1-XXX/170-PP	1"	2.4	60	18.9	480	2.3	59	3.8	97	8.5	3.9	3.3	0.2	1.57	0.5	0.2				
CSUASTD-D-1-XXX/170-CV1-PP																				

**Model Number Selection**

XXX refers to the desired closing temperature for standard balancing. When the water temperature drops below this point the CircuitSolver® will begin to open, allowing water to easily enter the return line. The valve will start to reopen approximately 20°F above the standard balancing temperature and rebalance the system at 170°F. For example, if you want 120°F desired return temperature and the CSUASTD-D-PP is to be installed on a 3/4" line, the model number would be CSUASTD-D-3/4-120-170-PP. To add optional check valve insert -CV1 to the end of the model number. Ex. CSUASTD-D-3/4-120-170-CV1-PP

MATERIALS		
		
ITEM	DESCRIPTION	MATERIAL
1	Valve Body w/ Union Threads	300 series stainless steel
2	Insert - CircuitSolver <sup>®</sup>	300 series stainless steel
3	Spring	300 series stainless steel
4	Plug	300 series stainless steel
5	Thermal Actuator	300 series stainless steel
6	Carrier	300 series stainless steel
7	Union Nut	300 series stainless steel
8	O-ring	BUNA
9	Check Valve (optional)	GLASS FILLED NORYL
10	Insert - Female Threaded	300 series stainless steel

OPTIONAL CHECK VALVE	
<b>Features and Benefits</b>	
-100% factory tested drip tight operation	
-Snap fit design, no retainer needed	
-Extra-low head loss and low cracking pressure	
-External O-ring in groove	
<b>Certifications</b>	
-ANSI/ NSF 61	
ITEM	MATERIAL
Cap	Glass filled Noryl
Guide	Glass filled Noryl
Plunger	Glass filled Noryl
Lip Spring	EPDM rubber
Spring	Stainless Steel AISI 301
O-ring	EPDM rubber

OPTIONAL CHECK VALVE TECHNICAL DATA	
Medium: Clear water only	
Approximate Cracking Pressure: 0.29 PSI	
<div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> <p>Continuous</p>  <p>max. 120 °C    max. 250 °F</p> </div> <div style="text-align: center;"> <p>Short-term (5 minutes max.)</p>  <p>max. 125 °C    max. 260 °F</p> </div> </div> <div style="display: flex; justify-content: space-around; margin-top: 5px;"> <div style="text-align: center;"> <p>150psi max.    10bar max.</p> </div> <div style="text-align: center;"> <p>230psi max.    16bar max.</p> </div> </div>	

FLOW RATE CALCULATION USING "Cv" FACTOR	
$GPM = C_v \sqrt{\Delta P}$	$C_v = \frac{GPM}{\sqrt{\Delta P}}$
	$\Delta P = \left[ \frac{GPM}{C_v} \right]^2$

### TYPICAL SPECIFICATION

- I. Furnish and install CIRCUITSOLVER<sup>®</sup> as indicated on the plans. CIRCUITSOLVER<sup>®</sup> shall be self-contained and fully automatic without additional piping or control mechanisms. Valve shall be a CIRCUITSOLVER<sup>®</sup> as manufactured by ThermOmegaTech<sup>®</sup>, Inc. or equivalent.
  - A. CIRCUITSOLVER<sup>®</sup> shall regulate the flow of recirculated domestic hot water based on water temperature entering the CIRCUITSOLVER<sup>®</sup> regardless of system operating pressure. As the water temperature increases the valve proportionally closes dynamically adjusting flow to meet the specified temperature.
    1. CIRCUITSOLVER<sup>®</sup> never fully closes, even at the desired set point. There is always sufficient bypass flow back to the recirculating pump to prevent overheating or "dead heading" of the pump.
    2. CIRCUITSOLVER<sup>®</sup> is set at the factory for the desired return temperature. No field adjustments needed. Several temperature set points are available.
    3. CIRCUITSOLVER<sup>®</sup> Thermal Disinfection Dual Balancing Assembly with Strainer (CSUASTD-D) shall be available in 1/2", 3/4" & 1" NPT.
  - B. CIRCUITSOLVER<sup>®</sup> Thermal Disinfection Dual Balancing Assembly with Strainer allows for an additional balancing cycle at 170°F.
    1. The valve will start to re-open above the low temperature balancing set point to allow high temperature water through during a thermal disinfection process. The valve will rebalance at the second temperature set point.
- II. CIRCUITSOLVER<sup>®</sup> body and all internal components are made with lead-free materials with major components constructed of type 300 series stainless steel.
  - A. CIRCUITSOLVER<sup>®</sup> shall be rated to 200 PSIG maximum working pressure.
    1. CIRCUITSOLVER<sup>®</sup> shall be standard tapered female pipe thread, NPT.
  - B. CIRCUITSOLVER<sup>®</sup> shall be rated to 250°F (121.1°C) maximum working temperature.
  - C. Thermal actuator shall be spring-loaded and self-cleaning, delivering closing thrust sufficient to keep orifice opening free of scale deposits.
- III. Installation of CIRCUITSOLVER<sup>®</sup> shall be made by qualified tradesmen. Install CIRCUITSOLVER<sup>®</sup> in each domestic hot water return piping branch beyond last hot water device in that branch.
  - A. Provide suitable line size isolation valves, unions, and strainer as indicated in piping detail shown on the drawings.
  - B. Provide suitable access panel as required in non-accessible ceilings and walls.
  - C. Pay close attention to flow arrow, especially with valves that have an integrated check valve.